



Pass and Seymour  
Trademaster® 15A/125V Duplex Receptacle, Brown  
Part No. 3232



Our Pass and Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.

## Features & Benefits

Durable, high-quality construction

125-volt outlet

Wire Size: #12 - #14 AWG, Solid wire

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Residential	Application Sector	Residential/Commercial
Standard	UL 498	Type	Outlet

### Dimensions

Product Width US	1.32 in	Product Depth US	0.96 in
Product Height US	4.2 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Additional Information

---

Product Environmental Profile Yes

---

## Technical Information

---

Connection	Wire Ground	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		

---