



Pass and Seymour  
Trademaster® 15A 125V Tamper-Resistant Duplex Receptacle, Black  
Part No. 3232TRBK



15A/125A Trademaster® Tamper-Resistant Duplex Receptacle

## Features & Benefits

Quality Materials, durability, and time-tested design

Rated 15 amperes

Wire Size: #12 - #14 AWG, Solid wire

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Residential, Tamper-Resistant
Type	Outlet		

### Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Is Tamper-Resistant	Yes	Amperage	15 A
---------------------	-----	----------	------

---

Number of Poles	Double Pole	Wire Size	14 - 12 AWG
-----------------	-------------	-----------	-------------

---

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

---