

## Pass and Seymour Trademaster® 15A 125V Self-Grounding Tamper-Resistant Duplex Receptacle, White Part No. 3232TRSW



15A/125A Trademaster® Self-Grounding, Tamper-Resistant Duplex Receptacle

## Features & Benefits

Quality Materials, durability, and timetested design

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

## Specifications

Ge	n 0	ral	In	fo
Ge.	ne	ıaı	- 111	HΟ

Product Line	Pass & Seymour	Color	White		
Finish	Matte	Country Of Origin	China		
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Residential, Self-Grounding, Tamper-Resistant		
Application Sector	Residential	Standard	cULus UL498, CSA C22.2 No. 42		
Туре	Outlet				
Dimensions					
Product Width US	1.32 in	Product Depth US	1.0 in		
Product Height US	3.31 in				
Listing Agencies / 3rd Party Agencies					

Yes

cULus Listed

Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Is Tamper-Resistant	Yes	Temperature Rating	-30° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		