



Receptacle Single 30A 120/208V 3-Phase-y

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL498

Dimensions

Product Width US	1.437 in	Product Depth US	1.2 in
Product Height US	2.25 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	Three	Number of Wires	4
Amperage	30 A	Number of Poles	4-Way
Wire Size	14 - 10 AWG	Voltage	3 to 120 V
Environmental Conditions	Consult the Factory		
