

Pass and Seymour 50A 250V 6-50R Straight Blade Single Surface Receptacle, 2-Pole, 3-Wire Part No. 3852

Durability.

Straight Blade Receptacle 2-Pole Wire 50A 250V



## Features & Benefits

Quality Materials.

Time-tested Design.

## Specifications

## General Info

| Product Line                 | Pass & Seymour | Color            | Black       |
|------------------------------|----------------|------------------|-------------|
| Country Of Origin            | China          | Standard         | UL 498      |
| Dimensions                   |                |                  |             |
| Product Width US             | 2.8 in         | Product Depth US | 2.41 in     |
| Product Height US            | 5.65 in        |                  |             |
| Listing Agencies / 3rd Party | Agencies       |                  |             |
| cULus ListingNumber          | 140596         | cULus Listed     | Yes         |
| Technical Information        |                |                  |             |
| Connection                   | Wire Ground    | Number of Wires  | 3           |
| Amperage                     | 50 A           | Number of Poles  | Double Pole |

| Wire Size | 4 | Voltage |  |
|-----------|---|---------|--|
|           |   |         |  |