

Pass and Seymour 15A NEMA L615 Single Receptacle

Part No. 4560

Receptacle Single 15A 250V Turnlok®



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info					
Product Line	Pass & Seymour	Country Of Origin	Mexico		
Application Sector	Industrial	Standard	UL 498		
Dimensions					
Product Depth US	0.922 in	Product Height US	2.375 in		
Listing Agencies / 3rd Party Agencies					
CSA Listed	Yes	cULus Listed	Yes		
CSA File Number	NO				

Additional Information

Product Environmental Profile	Yes		
Technical Information			
Phase	Single	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	18 - 0 AWG	Voltage	250.0 V