




Quiktron  
10ft Q-Series Cat6a Snagless (UTP) Ethernet Network Patch Cable, CM Rated - Yellow  
Part No. 576-A15-010



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

## Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

## Specifications

### General Info

|                   |                   |                    |                       |
|-------------------|-------------------|--------------------|-----------------------|
| Product Line      | Quiktron          | UPC Number         | 884815793445          |
| Country Of Origin | Vietnam           | Application Sector | Commercial/Industrial |
| Type              | Copper Patch Cord |                    |                       |

### Dimensions

|                   |         |                   |         |
|-------------------|---------|-------------------|---------|
| Product Weight US | 0.35 lb | Product Length US | 10.0 FT |
|-------------------|---------|-------------------|---------|

### Additional Information

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|