



Pass and Seymour
Turnlok® 67W47 Watertight Single Receptacle, Yellow
Part No. 67W47



Turnlok Watertight Single Receptacle, 20amp 125volt, NEMA Configuration L5-20, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed

Dimensions

Product Width US	1.85 in	Product Depth US	4.03 in
Product Height US	1.85 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Phase	Single	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole

Wire Size

14 - 10 AWG

Voltage

125.0 V

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,
66, 67 (Plug & Connector only) Flammability
UL94V0 (boxes & wiring device interiors) Operating
Temperature -40°C (without impact) to +60°C
continuous UV resistance All exposed material s
are UV stabilized
