



Pass and Seymour
Turnlok® 69W48 Watertight Single Receptacle, Yellow
Part No. 69W48



Turnlok Watertight Single Receptacle, 30amp 250volt, NEMA Configuration L6-30, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed

Dimensions

Product Width US	1.85 in	Product Depth US	4.75 in
Product Height US	1.85 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Phase	Single	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole

Wire Size	14 - 10 AWG	Voltage	250.0 V
-----------	-------------	---------	---------

Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized		
--------------------------	---	--	--
