

## Pass and Seymour 20A Non-NEMA Plug - Black Back, White Front Body

Part No. 7411SS

Medium-Duty Dead Front Connector, Black



## Features & Benefits

Quick-thread assembly screws and cord-grip Industrial-strength, brass alloy plug blades and connector contacts resist screws come backed-out, ready-to-wire. heat rise, provide excellent conductivity.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Double dovetail design provides superior protection against cord pull-out forces.

Impact- and corrosion-resistant durable nylon 6 shell material.

Rounded back contour reduces snags and hang-ups on the job site.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible Integral flexible rubber cord grommet conforms to and seals around SO cord assurance of safe and proper cord retention. to provide protection from oils, water, or chips entering wiring chamber.

## **Specifications**

General Info			
Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498		
Dimensions			
Product Width US	2.2 in	Product Length US	2.57 in
Technical Information			
Number of Wires	3	Amperage	20 A

Number of Poles	Double Pole	Wire Size	4
Voltage	250.0 V		