




radiant Collection  
radiant® Outdoor Outlet, Ivory  
Part No. 885TRWRI



Take a step up from the standard, even outside. This weather-resistant\* outlet installs easily to bring power to your patio, pool area, porch or deck, while elevating your outdoor space with the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. \*Must be installed in weatherproof enclosure per NEC requirements.

More color options available to fit any style.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Ivory	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Outdoor, Residential
Application Sector	Residential/Commercial	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
Product Height US	4.2 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed                      Yes

---

## Additional Information

---

Product Environmental Profile    Yes

---

## Technical Information

---

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Outdoor
-----------------	-------------	----------------	---------

---

Mounting Type	Box	Voltage	125.0 V
---------------	-----	---------	---------

---