



**Cablofil**  
**CabloPort Block 5" Long [943523]**  
 Part No. 943523



Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

## Features & Benefits

**Non Penetrating Weather Resistant Bases:** 100% recycled bases won't deteriorate over time. UV resistant rubber supports 1000lb/ft. Composite material accepts screws or other mechanical fasteners. Choice of two base styles -- standard or widebody.

**Pre-installed Supports:** Multiple support options designed to speed installation. Slotted Channel supports ladder tray, wire mesh tray and tubing. Metal supports available in 3 finishes: Pre-galvanized (PG, Standard), Hot-Dipped Galvanized (GC, Optional), and 304L Stainless Steel (S4, Optional).

**Wide Variety of Support Options:** Height adjustability bridges rooftop gaps, structures, or other utility pathways. Angled to adapt to any roof pitch. Multiple level for stacking cable pathways.

**Extends Life of Roof:** Rubber base cushions heavy metal supports. Standard or Widebody styles reduce pressure points on sensitive roofing materials. Dampens vibrations.

**Improves Safety:** Reflective safety strip keeps cable pathways visible on dark roofs and in low light conditions.

**Green Buildings:** 100% recycled rubber construction assists with building qualification for LEED credits.

**Fast Shipment:** Most assemblies ship in 1-3 days ARO.

## Specifications

### General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388019089	Country Of Origin	Canada
Application Sector	Commercial	Type	Fasteners

### Dimensions

Product Width US	6.0 in	Product Weight US	2.5 lb
Product Volume US	0.069 cu ft	Product Depth US	5.0 in

---

Product Height US                    4.0 in

---

**Buy American Act Compliance**

---

BAA                                        Yes

---