



**Cablofil**  
**CabloPort Block with FASP 24" Long [943531]**  
 Part No. 943531



Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

## Features & Benefits

Flat roof support: For support of tray, piping or other items on flat roofs.

Two support styles: FAS Profile for wire mesh trays or 13/16' galvanized channel (14 ga.) for ladder tray, piping or other material support.

Install: on any roofing material or other flat surface.

Supports are available in: one standard finish and two optional finishes.

Curb style maximum load: 750 lbs. (CPP5 and CPS5 - maximum load 200 lbs.).

Two rubber base designs: Standard Curb and Widebody style

Widebody design: has 1,000 lbs/ft maximum load and provides 5 times the surface area to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.

## Specifications

### General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388019164	Country Of Origin	United States
Application Sector	Commercial	Type	Fasteners

### Dimensions

Product Width US	6.0 in	Product Weight US	9.7 lb
Product Volume US	0.417 cu ft	Product Depth US	24.0 in
Product Height US	5.0 in		

---

## Buy American Act Compliance

---

BAA	Yes
-----	-----

---