

## 8K ULTRA HIGH SPEED HDMI CABLE



The Ultra High-Speed (48Gbps) HDMI cables support 8K at 60Hz and 4K at 120Hz with each length in-wall rated (CL3/Ft4). The cable supports high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD and Dolby Atmos®.

### Features & Benefits

Supports 8K at 60Hz and 4K at 120Hz

CL3/FT4 Rated for in-wall use

Sure Grip connector provides a firm grip to prevent cable damage

Enhanced retention clips keep the cable firmly in place

Gold Plated Connector resists corrosion and provides the highest level of signal conductivity

Enhanced Audio Return Channel (eARC): Supports high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD and Dolby Atmos®

### Specifications

#### General Info

Product Line	On-Q	Color	Black
Finish	Matte	Country Of Origin	China

#### Dimensions

Product Width US	0.87 in	Product Weight US	0.87 lb
Product Height US	10.16 in	Product Length US	8.66 in

#### Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Video Resolution	8K 60Hz
Jacket Application	In-Wall Rated	Cable Type	Ultra High Speed HDMI

---

Jacket Rating

CL3 Rated, FT4 Rated

Data Transfer Rate

48 Gbps

---

Connector Type

HDMI

Conductor Material

Gold

---

Environmental Conditions

0.9

---