



Turn lights on or off, or even dim them, with just a soft tap of a finger thanks to inventive micro-movement technology. Plus, as a Tru-Universal Dimmer, this dimmer switch self-calibrates to work with virtually any 120V dimmable bulb or fixture (excludes 0-10V). Always adjust to the precise light level you want, without the flicker.

This dimmer* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required.

Perfect for adding precise light level control – all it takes is a soft tap to turn on/off or adjust brightness.

Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

Usable in both single-pole and 3-way applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Graphite
Finish	Frosted	Country Of Origin	China
Features	Antimicrobial Protection, Indicator Lights	Switch Type	sofTap
Number of Switches	1	Application Sector	Residential

Warranty Type	Limited Lifetime Warranty	Type	Dimmer
---------------	---------------------------	------	--------

Dimensions

Product Width US	1.79 in	Product Depth US	1.77 in
Product Height US	4.2 in		

Technical Information

Electrical Rating	120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 700W (Halogen), 120V 700W (Incandescent), 120V 8A (EFL)	Number of Gangs	1
Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon	Number of Poles	Single Pole 3-Way
Indoor/Outdoor	Indoor	Wattage	700 W
Mounting Type	Box	Voltage	120.0 V
Connection Type	Internal Pressure Plates		
