



adorne Collection
adorne® 15A Tamper-Resistant Dual-Controlled Outlet, Magnesium
Part No. ARCD152M10



A modern upgrade for style, safety and energy management, this tamper-resistant, dual-controlled outlet from the adorne Collection installs easily in place of an existing outlet. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Independently cut power to either plug when not in use to conserve energy.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Magnesium	Finish	Frosted
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Indoor, Residential, Tamper-Resistant	Application Sector	Residential
Standard	CULUS	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

Dimensions

Product Width US	1.77 in	Product Depth US	1.73 in
------------------	---------	------------------	---------

Product Height US 2.12 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Is Tamper-Resistant Yes Phase Single

Connection Side and Back Wire Number of Wires 3

Number of Gangs 1 Amperage 15 A

Number of Poles Double Pole Wire Size 14 - 10 AWG

Indoor/Outdoor Indoor NEMA Configuration Code 5-15R

Mounting Type Box Voltage 125.0 V

Connection Type Internal Pressure Plates Environmental Conditions 95% (relative humidity, non-condensing)
