




adorne Collection  
adorne® 20A One-Gang Pop-Out Outlet, Graphite  
Part No. ARPTR201GG2



The cleverest way to add power and style, the Pop-Out Outlet extends to offer 2-plug access, then uniquely disappears back into the wall with a simple push when not in use. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Provides 2-plug access when extended from wall.

Installs easily in as little as 15 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Perfect anywhere you'd like to hide outlets when not in use, for added style and safety.

Disappears back into the wall with a simple push when not needed.

Comes with a special frame for mounting and requires a deep electrical outlet (22.5 cubic inches). No new wires required for typical installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Graphite	Country Of Origin	China
Number of Receptacles	3	Features	Pop-Out
Outlet Type	Indoor, Pop-Out, Residential, Tamper-Resistant	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

### Dimensions

---

Product Width US	2.99 in	Product Depth US	2.6 in
------------------	---------	------------------	--------

---

Product Height US	4.88 in
-------------------	---------

---

### Technical Information

---

Number of Gangs	1	Amperage	20 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

---

NEMA Configuration Code	5-20R	Mounting Type	Box
-------------------------	-------	---------------	-----

---

Voltage	125.0 V	Connection Type	Internal Pressure Plates
---------	---------	-----------------	--------------------------

---

Environmental Conditions	95% (relative humidity, non-condensing)
--------------------------	---

---