




adorene Collection

adorene® 20A Tamper-Resistant Ultra-Fast Plus Power Delivery USB Type-C/C Outlet, Plus-Size, Magnesium

Part No. ARTRUSB20PD30M4



Charge phones, tablets and more up to 40% faster, with Ultra-Fast USB Outlets from the adorene® Collection. Made to deliver a leading 6 amps of power, it provides a fast, future-proof solution for convenient in-wall charging without an adapter. Easily replacing traditional outlets in as little as ten minutes, this Ultra-Fast USB Outlet transforms your space with modern functionality and the unique, contemporary aesthetic of adorene. Made exclusively for use with screwless Wall Plates from the adorene® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorene® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Built for intelligent charging, the outlet detects and delivers the precise amount of power needed to maximize charging speeds.

Helpful indicator light lets you see charging status at a glance. Light glows yellow while charging is in progress, and shows green once the device battery is sufficiently charged.

Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Charges the latest devices up to 2X faster, thanks to the industry-leading 6.0A of our Ultra-Fast line and a whopping 30W of power courtesy of advanced Power Delivery.

Provides fast and convenient built-in charging through two future-proof USB Type-C ports, accommodating new and upcoming devices without an adapter.

Includes multiple layers of overcurrent protection, ensuring the outlet and your favorite devices can charge at optimal levels without risk of damage.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Magnesium	Finish	Frosted
Country Of Origin	China	Number of Receptacles	2
Features	USB-C Charging	Outlet Type	Indoor, Residential, Tamper-Resistant, USB-Charging
Application Sector	Residential/Commercial	Warranty Type	Limited Lifetime Warranty
Type	Tamper-Resistant, USB		

Dimensions

Product Width US	2.5 in	Product Depth US	1.77 in
Product Height US	3.0 in		

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

USB Amperage	6 A	Connection	USB Type C/C
Number of USBs	2	Output Current	6A
USB Power Output	30 W	Amperage	20 A
Current Rating	20 A	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Connection Type	Internal Pressure Plates
Environmental Conditions	95% (relative humidity, non-condensing)		
