




adorne Collection
adorne® 15A Paddle Switch, Magnesium, with Microban®
Part No. ASPD1532M4



With its twist on classic up-and-down switch control, this modern light switch lets you turn lights on and off with ease. Use the 15A paddle switch on its own to control a light or fixture from a single location, or pair with a second switch to control a single light source from two locations (3-way control).

This switch* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Country Of Origin	China	Features	Antimicrobial Protection
Switch Type	Paddle	Number of Switches	1
Standard	cULus	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.77 in	Product Depth US	1.5 in
------------------	---------	------------------	--------

Product Height US	1.77 in
-------------------	---------

Technical Information

Connection	Screw Terminals	Number of Gangs	1
------------	-----------------	-----------------	---

Amperage	15 A	Number of Poles	3-Way, Single Pole
----------	------	-----------------	--------------------

Mounting Type	Box	Voltage	120.0 V
---------------	-----	---------	---------

Connection Type	Internal Pressure Plates
-----------------	--------------------------
