



Pass and Seymour  
Strain Relief Grips  
Part No. BOX40



Wide Range, Straight Male, Dust Tight Grip, 1/2-inch, 0.400-0.540.

## Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and Includes insulated power centers. bushing.

370 lbs breaking strength rating (in US lbs)

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)	Type	Dust Tight

### Dimensions

Product Width US	0.54 in	Product Length US	0.5 in
------------------	---------	-------------------	--------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

### Technical Information

Maximum Cable Range	0.4 in	Minimum Cable Range	0.54 in
---------------------	--------	---------------------	---------

Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
----------	-------------------------------	----------	--

---

Load

Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.

---