

Pass and Seymour Strain Relief Deluxe Cord Grips, 1/2-in NPT, 90-Degree Male Part No. CG40890

Cord Grip Male 90-Degree, 1/2-inch NPT, 0.375-inch-0.500-inch



Features & Benefits

Deluxe cord grips are woven of stainless steel mesh with an aluminum body for corrosion resistance.

They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding and to aliminate statistics.

to help absorb direct pull, to resist flexing and binding, and to eliminate strain.

They are recommended for indoor or outdoor use where subjected to moisture in the wiring of pendant stations, processing equipment, hand tools, and extension cord sets.

Deluxe grips are suitable for use in hazardous locations per Class I, Div. 2: Class II, Div. 1 & 2: and Class III, Div. 1 & 2.

Specifications

General Info				
Product Line	Pass & Seymour	Country Of Origin	Mexico	
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial	
Standard	UL/CSA Approval (consult factory)			
Dimensions				
Product Width US	0.5 in			
Listing Agencies / 3rd	d Party Agencies			
CSA Listed	Yes	CSA File Number	67507	
Technical Information				
Maximum Cable Range	0.44 in	Minimum Cable Range	0.5 in	

Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.		