



Pass and Seymour  
Strain Relief Deluxe Cord Grips, 3/4-in NPT, Straight Male  
Part No. CG610



Cord Grip Male Straight, 3/4-inch NPT, 0.500-inch-0.625-inch

## Features & Benefits

- Deluxe cord grips are woven of stainless steel mesh with an aluminum body for corrosion resistance.
- They are recommended for indoor or outdoor use where subjected to moisture in the wiring of pendant stations, processing equipment, hand tools, and extension cord sets.
- They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain.
- Deluxe grips are suitable for use in hazardous locations per Class I, Div. 2: Class II, Div. 1 & 2: and Class III, Div. 1 & 2.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

### Dimensions

Product Width US	0.625 in
------------------	----------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

### Technical Information

Maximum Cable Range 0.56 in		Minimum Cable Range 0.625 in	
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.		