

Pass and Seymour Strain Relief Deluxe Cord Grips, 3/4-in NPT, 90-Degree Male Part No. CG61290

Cord Grip Male 90-Degree, 3/4-inch NPT, 0.625-inch-0.750-inch



Features & Benefits

| Deluxe cord grips are woven of stainless steel mesh with an aluminum body for corrosion resistance. | They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain. |
|--|--|
| They are recommended for indoor or outdoor use where subjected to moisture in the wiring of pendant stations, processing equipment, hand tools, and extension cord sets. | Deluxe grips are suitable for use in hazardous locations per Class I, Div. 2: Class II, Div. 1 & 2: and Class III, Div. 1 & 2. |

Specifications

General Info

| Product Line | Pass & Seymour | Country Of Origin | Mexico |
|-----------------------|--|---------------------|------------|
| Construction | Various Types of Pulling, Support and Strain Relief Grips | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |
| Dimensions | | | |
| Product Width US | 0.75 in | | |
| Listing Agencies / 3r | d Party Agencies | | |
| CSA Listed | Yes | CSA File Number | 67507 |
| Technical Information | n | | |
| Maximum Cable Range | 0.67 in | Minimum Cable Range | 0.75 in |
| | | | |

| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
|----------|--|----------|---|
| Load | Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure. | | |