



Pass and Seymour
Nylon Cord Grip, 3/4-in NPT 90-Degree, Oval UF Cable, .218-.640 OD Range
Part No. CGN759064UF



Non-Metallic Cord Connectors are constructed of a durable, nylon material which offers excellent corrosion resistance, is lightweight, durable and ideal for use in damp environments. Nylon Cord Connectors are ideally suited for use in applications with moisture or washdowns and they provide an environmental seal against dirt, coolants, as well as other chemicals.

Features & Benefits

Heavy duty Nylon body is resistant to impact and corrosion

Available in straight, 90°, and underground feed styles

Rugged construction suitable for various industrial applications such as MRO, food processing, water/waste water, marine, pulp & paper, and petrochemical

Rubber grommet provides a liquid-tight seal and reduces cord pull-out while resisting chemicals

Color coded grommets make for easy identification and ease of installation

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Nylon Cord Grip	Application Sector	Commercial/Industrial
Standard	UL Listed		

Listing Agencies / 3rd Party Agencies

CSA Listed Yes

Technical Information

Maximum Cable Range 0.625 in Minimum Cable Range 0.75 in