

On-Q In-Wall TV Power and Cable Management Kit, Canada, White Part No. CPT306WC1



This Legrand pre-wired kit is the perfect hassle-free solution for installers and homeowners who want to hide power and AV cables without the need for modifying electrical wiring. With this kit, extending power for a wall-mounted TV is a breeze, providing the ultimate flexibility while maintaining a clean and sleek appearance. The kit comes with an innovative decorator-based power inlet strap and a recessed box with a duplex power receptacle, providing an easy solution for concealed cabling inside the wall. This kit is ideal for those who want to enhance their home theater or office space while maintaining a professional and organized appearance.

Features & Benefits

Extend power to a wall mount TV without modifying the homes existing electrical wiring	Tamper Resistant receptacle powers multiple devices such as a TV, sound bar or streaming players
Recessed receptacle supports almost any type of power plug including right angles and wall warts	Unique decorator based power inlet strap provides flexible project support for ganging other AV connections
Hides both power and AV cables inside the wall for a clean, professional installation	Kit Includes: Recessed wall plate with integrated LV brush opening, junction box, 15A tamper resistant outlet and wall plate and the recessed box with duplex power receptacle.
Canadian Compliant - includes grounding clip	Wire Size: 14 - 2 AWG with Ground In - Wall Rated

Specifications

General Info

Product Line	On-Q	Color	White
Finish	Glossy	Country Of Origin	China
Receptacle Type	5-15R	Number of Receptacles	2
Outlet Type	Indoor, Residential, Tamper- Resistant	Package Quantity	1
Application Sector	Residential	Standard	cUL
Warranty Type	1-Year	Туре	Power Supply, Tamper- Resistant

Dimensions						
Product Width US	4.1 in	Product Weight US	2.16 lb			
Product Depth US	8.75 in	Product Height US	4.1 in			
Product Length US	10.25 in					
Listing Agencies / 3rd Party Agencies						
cUL ListingNumber	514C & 498	cUL Listed	Yes			
Technical Information						
ls Tamper-Resistant	Yes	Number of Gangs	2			
Temperature Rating	32° - 122° F	Amperage	15 A			
Number of Poles	3-Way	Wire Size	14 - 2 AWG			
Indoor/Outdoor	Indoor	Voltage	125.0 V			
Connection Type	Wired					