



**Wiremold**  
**Field Wired deQuorum Single Flip Up Unit with USB**  
Part No. DQFF15UST



Field wired unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Comes with a brushed stainless steel finish.

## Features & Benefits

**Sleek, Attractive Design:** Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

**Tamper-Resistant Receptacles:** Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

**New Soft Opening Cover Mechanism:** Opening and closing the cover is quieter and easier with a more professional feel.

**Expanded Configuration Options:** Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

**UL Spill Water Protection:** Meets or exceeds UL 111 - Outline of Investigation for Multioutlet Assemblies. Eliminates risk of shock or short circuiting due to moisture entering device.

**USB Charging Capability:** Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

**Multiple Cover Finish Options:** Durable black powder coat and brushed stainless steel finishes blend with most decors.

**cULus Listed:** Meets UL US and Canadian Safety standards for Multioutlet Assemblies (File E15191, Guide PVGT).

## Specifications

### General Info

|                    |            |              |   |
|--------------------|------------|--------------|---|
| Product Line       | Wiremold   | UPC Number   | 786776186819  |
| Country Of Origin  | Mexico     | Construction | Various   |
| Application Sector | Commercial | Standard     | cULus Multioutlet Assembly File E15191 Guide PVGT Listed to US and Canadian Safety Standards. Meets Article 390 of the NEC. |
| Type               | Flip Up    |              |   |

### Dimensions

---

|                  |         |                   |          |
|------------------|---------|-------------------|----------|
| Product Width US | 4.75 in | Product Length US | 5.625 in |
|------------------|---------|-------------------|----------|

---

|               |        |                |             |
|---------------|--------|----------------|-------------|
| Knockout Size | 1/2 in | Cubic Capacity | 50.19 cu in |
|---------------|--------|----------------|-------------|

---

### Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E15191 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

### Buy American Act Compliance

---

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

---

### Additional Information

---

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

---

### Technical Information

---

|             |        |               |          |
|-------------|--------|---------------|----------|
| Cable Entry | Bottom | Mounting Type | Recessed |
|-------------|--------|---------------|----------|

---

|                   |   |
|-------------------|---|
| Number of Outlets | 2 |
|-------------------|---|

---