

Pass and Seymour Flexcor® Support Grips Standard Duty, Split Rod, Single Eye, Cable Diameter 1.75 - 1.99 in. Part No. FR175U

FR175U: Standard Duty, Split Rod, Single Eye, Cable Diameter 1.75 - 1.99 inches, Bale Length 14-in, Mesh Length 20-in, Break Strength 2640 lbs.

They are available in a variety of eye styles and cable ranges for supporting

Most Flexcor products have UL and/or CSA approvals. Please contact

electrical and fiber optic cable, metal rods, and tubing.

factory for approval information.



Features & Benefits

Split rod support grips are used when the end of the cable cannot be Split rod support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Bale Length: 14: Mesh Length: 20

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		
Technical Informatio	n		
Maximum Cable Range	1.75 in	Minimum Cable Range	1.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations

Load Approx. Break Strength: 2640