

Pass and Seymour Flexcor® Support Grips Standard Duty, Split Rod, Double-Eye, Cable Diameter 2.00 - 2.49 in. Part No. FR200UU

FR200UU: Standard Duty, Split Rod, Double-Eye, Cable Diameter 2.00 - 2.49 inches, Bale Length 6-in, Mesh Length 22-in, Break Strength 3750 lbs.



Features & Benefits

Split rod support grips are used when the end of the cable cannot be Split rod support grips are designed for loads up to 600 lbs. easily accessed and the installation is temporary.

Vertical runs of no more than 100 ft.

factory for approval information.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Most Flexcor products have UL and/or CSA approvals. Please contact

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Bale Length: 6: Mesh Length: 22

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	2 in	Minimum Cable Range	2.49 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 3760		