

Pass and Seymour Flexcor® Support Grips Standard Duty, Split Lace, Offset Eye, Cable Diameter 3.50 - 3.99 in. Part No. FS3500F

FS3500F: Standard Duty, Split Lace, Offset Eye, Cable Diameter 3.50 - 3.99 inches, Bale Length 9-in, Mesh Length 28-in



Features & Benefits

Split lace support grips are used when the end of the cable cannot easily be
accessed and the support grip is intended for permanent installation.Split lace support grips are designed for loads up to 600 lbs.Vertical runs of no more than 100 ft.They are available in a variety of eye styles and cable ranges for
support grips are woven of corrosion-resistant tinned-stainless steel wire.Most Flexcor products have UL and/or CSA approvals. Please
contact factory for approval information.

Bale Length: 9: Mesh Length: 28

Specifications

General Info

| Product Line | Pass & Seymour | Country Of Origin | Mexico |
|-----------------------|--|---------------------|---|
| Construction | Various Types of Pulling, Support and Strain Relief Grips | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |
| Technical Information | | | |
| Maximum Cable Range | 3.5 in | Minimum Cable Range | 3.99 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Approx. Break Strength: 5040 | | |
| | | | |