



Wiremold

Plug-In Outlet Center Unit / Plug-In Outlet Center Unit / 250V/10A/5 IEC320 Female Outlets/Male IEC320 Input
Part No. IEC5



Five 250V, IEC 320 outlets, gray finish, 10A single pole circuit breaker, power cord not included. Length 11' (279mm). Receptacle center-to-center 1 1/2" (38mm). Input is provided with a male IEC320 Receptacle. Appropriate input cord must be purchased separately. Output receptacles are female IEC320. Snap-on, slide-off mounting. Power cord not included. NOTE: cULus Listed, TUV Nord Certified EN0950.

Features & Benefits

Five 250V, IEC 320 outlets, gray finish, 10A single pole circuit breaker, power cord not included. Length 11' (279mm). Receptacle center-to-center 1 1/2" (38mm). Input is provided with a male IEC320 Receptacle. Appropriate input cord must be purchased separately. Output receptacles are female IEC320. Snap-on, slide-off mounting. Power cord not included. NOTE: cULus Listed, TUV Nord Certified EN0950.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776100907
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	5	Application Sector	Commercial
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	2.0 in	Product Length US	11.0 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E173292	cULus Listed	Yes
---------------------	---------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformance	Yes
------------------	-----

Technical Information

Phase	Single	Frequency Rating	60 Hz
-------	--------	------------------	-------

Amperage	20 A	Enclosure Type	Aluminum
Mounting Type	Slide-off, Snap-on	Voltage	125.0 V
Environmental Conditions	Dry interior locations		
