

Turnlok® Duplex Receptacle 3-Wire 15A 125V Isolated Ground



Features & Benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate backwire capability. Accepts #14-#10 AWG.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Finish	Matte	Country Of Origin	Mexico
Receptacle Type	Locking	Number of Receptacles	2
Application Sector	Industrial	Standard	UL 498
Type	Isolated Ground		

Dimensions

Product Width US	1.5 in	Product Depth US	4.03 in
Product Height US	1.2 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

CSA File Number	16063
-----------------	-------

Technical Information

Phase	Three	Number of Wires	3
-------	-------	-----------------	---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	18 AWG	Voltage	125.0 V
-----------	--------	---------	---------
