




Pass and Seymour
20A 125/250V NEMA L1420 Single Receptacle, 4-Wire, Black
Part No. L1420R



Turnlok® Single Receptacle 4-Wire 20A 125/250V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Commercial, Indoor
Application Sector	Industrial	Standard	UL 498
Type	Outlet		

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	4 AWG	Indoor/Outdoor	Indoor
-----------	-------	----------------	--------

Voltage	125.0 V
---------	---------
