



Pass and Seymour  
30A NEMA L1430 Flanged Inlet, Gray  
Part No. L1430FI



Flanged Inlet 4-Wire 30A 125/250V Turnlok®

## Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Gray       |
| Country Of Origin | Mexico         | Application Sector | Industrial |
| Standard          | UL 498         |                    |            |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 3.12 in | Product Depth US | 1.75 in |
|------------------|---------|------------------|---------|

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 146159 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

|                 |   |          |      |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 30 A |
|-----------------|---|----------|------|

---

Number of Poles

Double Pole

Wire Size

4

---

Voltage

125.0 V

---