

## Pass and Seymour **20A NEMA Connector L2120 - Black Back, White Front Body** Part No. L2120C

Turnlok® Connector 5-Wire 20A 3-Phase 120/208V



## Features & Benefits

Quick-thread assembly screws and cord-grip Industrial-strength, brass alloy plug blades and connector contacts resist screws come backed-out, ready-to-wire. heat rise, provide excellent conductivity.

Raised ribs provide non-slip gripping profile D for turning to lock and unlock.

Double dovetail design provides superior protection against cord pull-out forces.

Impact- and corrosion-resistant durable nylon 6 shell material.

Rounded back contour reduces snags and hang-ups on the job site.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible Integral flexible rubber cord grommet conforms to and seals around SO cord assurance of safe and proper cord retention. to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

## General Info Product Line Pass & Seymour Color Black Country Of Origin **Application Sector** Industrial Mexico Standard UL 498 **Dimensions** Product Width US 2.2 in 3.33 in Product Length US Listing Agencies / 3rd Party Agencies cULus ListingNumber 146159 cULus Listed Yes

Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Phase	Three	Number of Wires	5
Amperage	20 A	Number of Poles	3-Way
Wire Size	18 - 0 AWG	Voltage	120.0 V