

## Pass and Seymour 30A L2130 Connector - Black Back, White Front Body

Part No. L2130C



Turnlok® Connector 5-Wire 30A 3-Phase 120/208V

## Features & Benefits

screws come backed-out, ready-to-wire.

Quick-thread assembly screws and cord-grip Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Double dovetail design provides superior protection against cord pull-out forces.

Impact- and corrosion-resistant durable nylon 6 shell material.

Rounded back contour reduces snags and hang-ups on the job site.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible Integral flexible rubber cord grommet conforms to and seals around SO cord assurance of safe and proper cord retention. to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

## General Info Product Line Black Pass & Seymour Color Country Of Origin Industrial Mexico **Application Sector** Standard UL 498 **Dimensions** Product Width US 2.2 in Product Length US 3.33 in Listing Agencies / 3rd Party Agencies cULus Listed cULus ListingNumber 146159 Yes

Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Phase	Three	Number of Wires	5
Amperage	30 A	Number of Poles	3-Way
Wire Size	18 - 0 AWG	Voltage	120.0 V