

Pass and Seymour 30A L2130 Plug - Black Back, White Front Body

Part No. L2130P



Turnlok® Plug 5-Wire 30A 3-Phase 120/208V

Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Impact- and corrosion-resistant durable nylon 6 shell material.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Double dovetail design provides superior protection against cord pull-out forces.

Rounded back contour reduces snags and hang-ups on the job site. \\

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible Integral flexible rubber cord grommet conforms to and seals around SO cord assurance of safe and proper cord retention. to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info Product Line Pass & Seymour Color Black Country Of Origin Mexico **Application Sector** Industrial UL 498 Standard **Dimensions** Product Width US 2.57 in 2.2 in Product Length US

May 19 2024 - For latest specs visit <u>www.legrand.us</u>

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Phase	Three	Number of Wires	5
Amperage	30 A	Number of Poles	3-Way
Wire Size	18 - 0 AWG	Voltage	120.0 V