

Pass and Seymour 20A NEMA Connector L520 - Black Back, White Front Body Part No. L520C

Turnlok® Connector 3-Wire 20A 125A



Features & Benefits

screws come backed-out, ready-to-wire.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Impact- and corrosion-resistant durable nylon 6 shell material.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

Quick-thread assembly screws and cord-grip Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

> Double dovetail design provides superior protection against cord pull-out forces.

Rounded back contour reduces snags and hang-ups on the job site.

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible Integral flexible rubber cord grommet conforms to and seals around SO cord assurance of safe and proper cord retention. to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info					
Product Line	Pass & Seymour	Color	Black		
Country Of Origin	Mexico	Application Sector	Industrial		
Standard	UL 498				
Dimensions					
Product Width US	2.2 in	Product Length US	3.33 in		
Listing Agencies / 3rd Par	ty Agencies				
cULus ListingNumber	146159	cULus Listed	Yes		

Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	4
Voltage	125.0 V		