

Turnlok® Connector IP20 Suitability, 20A 480V, L8-20R



Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
Raised ribs provide non-slip gripping profile for turning to lock and unlock.	Double dovetail design provides superior protection against cord pull-out forces.
Impact and corrosion-resistant durable nylon 6 shell material.	Rounded back contour reduces snags and hang-ups on the job site.
Scallop shell design provides non-slip gripping surface for insertion and withdrawal.	Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible Integral flexible rubber cord grommet conforms to and seals around SO cord assurance of safe and proper cord retention. to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info						
Product Line	Pass & Seymour	Color	Black			
Country Of Origin	Mexico	Application Sector	Commercial			
Standard	UL 498					
Dimensions						
Product Width US	2.2 in	Product Length US	3.33 in			
Listing Agencies / 3rd Party Agencies						
cULus ListingNumber	146159	cULus Listed	Yes			

Additional Information

Product Environmental Profile Yes

Technical Information

Phase	Three	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	18 - 10 AWG	Voltage	480.0 V