



Pass and Seymour  
Light Duty, Short Length, Flexible Eye  
Part No. PL1501



Light Duty, Short Length, Flexible Eye. Cable Diameter - 1.500-1.740-inch, Mesh Length - 16-inch, Break Strength - 7,500 lbs.

## Features & Benefits

Light-Duty grips are the most economical pulling grips for many applications, such as industrial plant wiring, and rewiring, and underground electrical pulls.

Mesh Length: 16

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

### Technical Information

Maximum Cable Range	1.5 in	Minimum Cable Range	1.74 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 7500		