



1-Pole Key Lock Back and Side-Wire 20A 120/277V

## Features & Benefits

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc. Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL20

### Dimensions

Product Width US	2.75 in	Product Height US	4.5 in
------------------	---------	-------------------	--------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Actuator	Toggle	Contact Rating	20Amp, 120/277V
Amperage	20 A	Action	SP
Number of Poles	Single Pole	Voltage	120.0 V