

## Pass and Seymour Industrial Extra Heavy Duty Specification Grade Switch, Lighted When On, Back and Side Wire, Red Part No. PS20AC1RPL



1-Pole Pilot Lighted Switch, Back and Side-Wire, 20A 277V

## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body Oversized silver alloy contacts for long life and better heat dissipation. separation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

# **Specifications**

## General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498/20		
Dimensions			
Product Width US	1.32 in	Product Depth US	1.073 in

3.281 in

Product Height US

cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Actuator	Toggle	Contact Rating	20Amp, 120Vac
Amperage	20 A	Action	Single pole
Number of Poles	Single Pole	Voltage	120.0 V