

# Pass and Seymour Industrial Extra Heavy Duty Specification Grade Switch, Ivory Part No. PS20AC2I



2-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V

#### Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of istallation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

## **Specifications**

### General Info

Product Line	Pass & Seymour	Color	lvory
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498/20		

#### **Dimensions**

Product Width US	1.32 in	Product Depth US	1.073 in	
Product Height US	3.281 in			
Listing Agencies / 3rd Party Agencies				
cULus ListingNumber	140597	cULus Listed	Yes	
Technical Information				
Actuator	Toggle	Contact Rating	20Amp, 120/277Vac	
Amperage	20 A	Action	Double pole	
Number of Poles	Double Pole	Voltage	120.0 V	