

Pass and Seymour Extra Heavy Duty Spec. Grade and Security Switches Part No. PS20AC2KL

1511 6

2-Pole Key Lock Back and Side-Wire 20A 120/277V

Features & Benefits

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum For compatible wall plate options, from security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc. Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info			
Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 20
Dimensions			
Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		
Listing Agencies / 3rd Pa	arty Agencies		
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Contact Rating	20Amp, 120/277Vac	Closed Contact Resistance	Toggle
Amperage	20 A	Number of Poles	Double Pole

Wattage	
---------	--