



3-Way Pilot Lighted Switch, Back and Side-Wire, 20A 120 Volt

## Features & Benefits

|  |   |
|--|---|
| External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors. | Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.   |
| Cam controls fast "make" and positive "break" to minimize arcing.  | Heavy-duty bumper pads for quiet operation.   |
| High strength thermoplastic polycarbonate toggle.  | Back body made of glass-reinforced nylon.   |
| Locking support provides resistance to face and back body separation.                                      | Oversized silver alloy contacts for long life and better heat dissipation.  |
| Grounding terminal is standard.  | Shallow design for ease of installation.  |
| Strap nickel-plated steel with integral ground.  | Auto-ground clip assures positive ground.   |
| For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .             | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> . |

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Clear      |
| Country Of Origin | Mexico         | Application Sector | Industrial |
| Standard          | UL 20          |                    |            |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.25 in  | Product Depth US | 1.09 in |
| Product Height US | 4.195 in |                  |         |

### Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

**Technical Information**

---

|                |                   |                           |         |
|----------------|-------------------|---------------------------|---------|
| Contact Rating | 20Amp, 120/277Vac | Closed Contact Resistance | Toggle  |
| Amperage       | 20 A              | Number of Poles           | 3-Way   |
| Wattage        | 3 W               | Voltage                   | 120.0 V |

---