



Pass and Seymour  
Industrial Extra Heavy Duty Specification Grade Lock Switch Back and Side Wire, Red  
Part No. PS20AC3REDL



3-Way Lock Switch, Back and Side-Wire, 20A 120/277V (Key can be removed in both positions)

## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 20		

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Contact Rating	20Amp, 120/277Vac	Closed Contact Resistance	Toggle
Amperage	20 A	Number of Poles	3-Way
Wattage	3 W	Voltage	120.0 V

---