



Pass and Seymour  
Extra Heavy Duty Spec. Grade 347VAC Toggle Switch Back and Side Wire, White  
Part No. PS371530W



Canadian 3-Way Switch, Back and Side-Wire, 15A 347V

## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | White      |
| Country Of Origin | Mexico         | Application Sector | Industrial |
| Standard          | UL 20          |                    |            |

### Technical Information

---

|                |               |                           |         |
|----------------|---------------|---------------------------|---------|
| Contact Rating | 15amp, 347vac | Closed Contact Resistance | Toggle  |
| Amperage       | 15 A          | Number of Poles           | 3-Way   |
| Wattage        | 3 W           | Voltage                   | 347.0 V |

---