



Pass and Seymour  
100A 3 Pole 4 Wire Fusible Mechanical Interlock  
Part No. PS4100FMIR5W



Triple pole, Four wire, Fusible Mechanical Interlock Receptacle. 100 amp, 3/600 vac.

## Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Industrial
Standard	UL Listed		

### Dimensions

Product Width US	11.13 in	Product Depth US	11.06 in
Product Height US	28.31 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

---

Phase	3	Number of Wires	4
Amperage	100 A	Number of Poles	3-Way
Voltage	600.0 V		

---