




Pass and Seymour
100A 3 Pole 4 Wire Fusible Mechanical Interlock
Part No. PS4100FMIR7W



Triple pole, Four wire, Fusible Mechanical Interlock Receptacle. 100 amp, 3/480 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | United States | Application Sector | Industrial |
| Standard | UL Listed | | |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 11.13 in | Product Depth US | 11.06 in |
| Product Height US | 28.31 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|----------|---------|-----------------|-------|
| Phase | 3 | Number of Wires | 4 |
| Amperage | 100 A | Number of Poles | 3-Way |
| Voltage | 480.0 V | | |
