



Pass and Seymour  
Non-Fusible Mechanical Interlock  
Part No. PS460MIR5W



Triple-Pole, 4-Wire, Non-Fusible Mechanical Interlock Receptacle.  
60A, 3, 600V.

## Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Commercial
Standard	UL Listed		

### Dimensions

Product Width US	9.13 in	Product Depth US	9.0 in
Product Height US	14.13 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	31169	cULus Listed	Yes
---------------------	-------	--------------	-----

### Technical Information

---

Phase	3	Number of Wires	4
Amperage	60 A	Number of Poles	3-Way
Wire Size	2 AWG	Voltage	600.0 V

---