



Pass and Seymour
Straight Blade PLUG 3W 15A 125V HG PS5266XHG
Part No. PS5266XHG



Straight Blade Hospital Grade Plug, double pole and three wire, unit arrives completely ready-to-wire, cutting installation time significantly. Its nylon housing provides impact and chemical resistance. Its rugged two-piece cord grip provides more uniform cord retention and the internal dust shield keeps terminals free of contaminants. 15amp 125volt.

Features & Benefits

Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

For covering patents, see www.legrand.us/patents.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Standard	UL 498

Dimensions

Product Width US	1.516 in	Product Length US	1.752 in
------------------	----------	-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connection	Wire Grounding	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	4	Voltage	125.0 V
